



Bilby 3D

MATERIAL DATA SAFETY SHEET

Issued in Australia by Bilby 3D Pty Ltd.

The attached Material Data Safety Sheet has been prepared by the manufacturer outside Australia.

In accordance with Australia WHS regulations the following Australian contact details apply

Section 1: AUSTRALIAN COMPANY DETAILS

In Australia the product is imported and distributed by:
Bilby 3D Pty Ltd

Mailing Address :

Kingsgrove Business Centre, 7/192 Kingsgrove Rd, Kingsgrove NSW 2208

Head Office Address :

Kingsgrove Business Centre, 7/192 Kingsgrove Rd, Kingsgrove NSW 2208

Contact Phone: 1800 847 333

Section 2: AUSTRALIAN EMERGENCY CONTACT

Emergency Contact

In the event of an emergency please contact:

Poisons Information Centre 24 hour Telephone Advice Line on 13 11 26


Section 3: AUSTRALIAN ISSUE DATA

Date of Issue : 1 March 2020



Photocentric
WASH 15

Technical Specifications



Maximum Part Size
300 x 275 x 120mm



140 Prints*
*Varies based on resin used
Number of prints per 15ltr of
Photocentric Cleaner will clean
in regular use without changing



15L Capacity
Photocentric Cleaner
volume to fill the wash unit

Printer compatibility	LC Precision 1.5, LC HR2
Dimensions	External: 280 (H) x 340 (D) x 330 (W) mm
	Internal: 120 (H) x 275 (D) x 300 (W) mm
Suggested Operating Environment	18-28°C
Agitation Method	30 x 40kHz transducers
Ultrasonic capabilities	Equippedd with 30 40kHz transducers capable of 1500W maximum power
Weigh	13kg

Included accessories

Lid	Outflow valve
Tank	Outflow pipe
Basket	Clip
Power Cable	Drainage cap
Instruction manual	

**Photocentric Resin cleaner only to be used with
this product**

Standard manufacturer warranty